

## FI7000 Probe Interface

### Features

The FI7000 interface provides both power to and communication with the FL/PL 7000 series probes. A low-level loop back fiber optic connection is used to sense unexpected disconnect of laser driven fibers to ensure user-safe operation. As an additional safety measure, shuttered connectors are used on all fiber optic connections to and from the probe.

The FI7000 can be used with the FM7004A Field Monitor (using the provided 0.5 meter fiber optic cable) or a PC by direct communication using the USB, GPIB, or RS-232 interfaces.



### Specifications

#### Interfaces:

IEEE-488 (GPIB)  
 USB 2.0, Test and Measurement class  
 RS-232 (19200 Baud)  
 Fiber Optic Serial (19200 Baud) reserved for connection to FM7004A Field Monitor  
 Laser Fiber Optic Serial reserved for connection to one FL/PL 7000 series probe

#### Fiber Optic Connectors:

(2) E2000 compact duplex female for probe communication and safety fiber loop  
 (2) FSMA for fiber connection to FM7004A

**Laser:** 500 mW, 830 nm

#### Laser shutdown time:

< 1 msec after fiber disconnect  
 < 250 msec after loss of communication

#### Power Requirements:

Input Voltage 90-260 VAC, 50-60 Hz  
 Input Current 0.2 - 0.6 A  
 Input type IEC inlet with filter

**Enclosure:** Desktop case, 2U high; 1U blank panel installed.

#### Dimensions (WxHxD):


without enclosure 48.3 x 4.5 x 25.4 cm (19.0 x 1.75 x 10.0 in)  
 with enclosure 49.8 x 12.7 x 30.5 cm (19.6 x 5.0 x 12.0 in)

#### Weight:

without enclosure 2.5 kg (6.25 lb)  
 with enclosure 7.25 kg (16 lb)

**Operating Temperature Range:** 10°C to 40°C (50°F to 104°F) @ 5% to 95% RH non-condensing

Model	Description
FI7000	Housed in a 2U instrument case
FI7000M1	Rack mount (Instrument case removed)



Complies with 21CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice # 50, dated June 24, 2007

AR RF/Microwave  
 Instrumentation  
 160 School House Rd  
 Souderton, PA 18964  
 215-723-8181

For an applications engineer call: 800.933.8181

[www.arworld.us](http://www.arworld.us)

To order AR Products, call 215.723.8181. For an applications engineer call: 800.933.8181. Direct to Service call: 215.723.0275 or email: [service@arworld.us](mailto:service@arworld.us) For Faxing Orders: 866.859.0582 (Orders Only Please) [info@arworld.us](mailto:info@arworld.us)  
 Approved for public release by AR RF/Microwave Instrumentation

020816